



C.I.P.	40 x 46 Country of Origin : US	TAB.	X																																																																
		Date	07-05-14																																																																
		Revision	08-04-15																																																																
	CARTRIDGE MAXIMALE																																																																		
	<table border="0"> <thead> <tr> <th></th> <th>Maxi</th> <th>Mini</th> <th></th> </tr> </thead> <tbody> <tr> <td>Culot</td> <td>dia. d = 41.15 mm</td> <td>40.90 mm</td> <td>(1)</td> </tr> <tr> <td>Bourrelet</td> <td>dia. g = 43.61 mm</td> <td>43.35 mm</td> <td></td> </tr> <tr> <td>Bourrelet</td> <td>ép. t = 1.93 mm</td> <td>1.77 mm</td> <td>(1)</td> </tr> <tr> <td>Tube</td> <td>dia. h = 40.51 mm</td> <td>40.26 mm</td> <td></td> </tr> <tr> <td>Length :</td> <td colspan="3"></td> </tr> <tr> <td>L max</td> <td colspan="2">= 110 mm</td> <td>Tolerance : -0.50 mm</td> </tr> </tbody> </table>		Maxi	Mini		Culot	dia. d = 41.15 mm	40.90 mm	(1)	Bourrelet	dia. g = 43.61 mm	43.35 mm		Bourrelet	ép. t = 1.93 mm	1.77 mm	(1)	Tube	dia. h = 40.51 mm	40.26 mm		Length :				L max	= 110 mm		Tolerance : -0.50 mm																																						
	Maxi	Mini																																																																	
Culot	dia. d = 41.15 mm	40.90 mm	(1)																																																																
Bourrelet	dia. g = 43.61 mm	43.35 mm																																																																	
Bourrelet	ép. t = 1.93 mm	1.77 mm	(1)																																																																
Tube	dia. h = 40.51 mm	40.26 mm																																																																	
Length :																																																																			
L max	= 110 mm		Tolerance : -0.50 mm																																																																
	CHAMBER MINIMALE																																																																		
	<table border="0"> <tbody> <tr> <td>Culot</td> <td>dia.</td> <td>D mini = 41.50</td> <td>+ 0.1 mm</td> <td>(1)</td> </tr> <tr> <td>Drageoir</td> <td>dia.</td> <td>G mini = 44.20</td> <td>+ 0.2 mm</td> <td></td> </tr> <tr> <td>Drageoir</td> <td>pro.</td> <td>T mini = 1.90</td> <td>± 0.05 mm</td> <td>(1)</td> </tr> <tr> <td>Chamber</td> <td>dia.</td> <td>H mini = 41.30</td> <td>± 0.05 mm</td> <td>(1)</td> </tr> <tr> <td>Barrel</td> <td>dia.</td> <td>B mini = 40.86</td> <td>+ 0.05 mm</td> <td>(1)</td> </tr> <tr> <td>Barrel</td> <td>angle</td> <td>α1 mini = 10°</td> <td></td> <td>(1)</td> </tr> <tr> <td>Length :</td> <td colspan="4"></td> </tr> <tr> <td>I max</td> <td colspan="2">= 49.10 mm</td> <td>Tolerance : +0.50 mm</td> <td>(1)</td> </tr> <tr> <td>E max</td> <td colspan="4">= 160 Joules</td> </tr> <tr> <td>EK</td> <td colspan="4">= 176 Joules</td> </tr> <tr> <td>Headspace</td> <td colspan="2">= 0.10 mm (Proof barrel)</td> <td></td> <td>(1)</td> </tr> <tr> <td></td> <td colspan="2">= 0.20 mm (with bascule)</td> <td></td> <td>(1)</td> </tr> <tr> <td></td> <td colspan="2">= 0.35 mm (automatic)</td> <td></td> <td>(1)</td> </tr> </tbody> </table>	Culot	dia.	D mini = 41.50	+ 0.1 mm	(1)	Drageoir	dia.	G mini = 44.20	+ 0.2 mm		Drageoir	pro.	T mini = 1.90	± 0.05 mm	(1)	Chamber	dia.	H mini = 41.30	± 0.05 mm	(1)	Barrel	dia.	B mini = 40.86	+ 0.05 mm	(1)	Barrel	angle	α1 mini = 10°		(1)	Length :					I max	= 49.10 mm		Tolerance : +0.50 mm	(1)	E max	= 160 Joules				EK	= 176 Joules				Headspace	= 0.10 mm (Proof barrel)			(1)		= 0.20 mm (with bascule)			(1)		= 0.35 mm (automatic)			(1)	
Culot	dia.	D mini = 41.50	+ 0.1 mm	(1)																																																															
Drageoir	dia.	G mini = 44.20	+ 0.2 mm																																																																
Drageoir	pro.	T mini = 1.90	± 0.05 mm	(1)																																																															
Chamber	dia.	H mini = 41.30	± 0.05 mm	(1)																																																															
Barrel	dia.	B mini = 40.86	+ 0.05 mm	(1)																																																															
Barrel	angle	α1 mini = 10°		(1)																																																															
Length :																																																																			
I max	= 49.10 mm		Tolerance : +0.50 mm	(1)																																																															
E max	= 160 Joules																																																																		
EK	= 176 Joules																																																																		
Headspace	= 0.10 mm (Proof barrel)			(1)																																																															
	= 0.20 mm (with bascule)			(1)																																																															
	= 0.35 mm (automatic)			(1)																																																															
Dimensions in « mm » Dimensions and tolerances for Proof Barrels : <div style="border: 1px solid blue; padding: 2px; display: inline-block; margin-top: 5px;">Annexe CR4</div>		Notes : 1) Check for safety reasons																																																																	